

# Ultralite Bakeables®



**PACTIV**  
Foodservice / Food Packaging

# Ultralite Bakeables®




## Freezer Safe, Oven Ready Bakeable Trays

Product can go from the freezer, to the oven, to the shelf, to the customers home all in the same package!

Ovenable trays have a high temperature tolerance.

Products can be baked up to 400 degrees F and frozen at -40 degrees F.

A wide variety of sizes for multiple baking applications, all with available high clarity after bake fit lids perfect for merchandizing product.



Item#	Description	Cube	Case Wt.	Case Pack	Ti/Hi
12263	4" Round 7 oz CPET cup	0.92	9.64	720	10x6
12266	4" Round 4 oz CPET cup	0.92	9.64	720	10x5
12528	4" Round After Bake Lid	2.46	8.17	720	9x5
13325	4 Cell Large Muffin CPET Base	1.05	19.12	240	15x7
13189APT	4 Cell Large Muffin Lid	3.67	14.2	240	5x6
13447	8" Square CPET Base	1.05	15.58	240	15x7
13190	8" Square After Bake Lid	3.31	12.53	240	6x6
13301	8" 48 oz Angel Food Pan Black CPET Base	3.88	26.19	280	5x4
11775	8" Angel Food Lid	3.88	13.62	280	4x5
13300	10" 82 oz Angel Food Pan Black CPET Base	4.01	29.88	200	5x6
11848	10" Angel Food Lid	4.01	12.09	200	6x5
13474	12" Pizza/Cookie Pan CPET Base	0.71	10.65	75	9x12
13246	12" CPET Lid	2.38	8.03	75	9x4
49159DO	15 oz Rectangle Black CPET Base Combo	2.24	14	250	6x5
49189DO	18 oz Rectangle Black CPET Base Combo	1.55	15.03	250	6x5
49329DO	32 oz Rectangle Black CPET Base Combo	2.2	24.68	250	10x4
49409DO	40 oz Rectangle Black CPET Base Combo	3.51	25.22	250	6x4

## Bakeables Use Instructions

**Cooking Temperature for Bakeables Containers:** 400°F or less. **Note:** Oven must be preheated prior to use.

**Use Instructions:** Containers can be used in conventional or microwave heating. Package may become brittle when frozen. If shipping frozen, stack and layer dividers in shipping carton are recommended.

**Conventional Oven Heating:** Preheat oven before placing container inside. Remove cover before heating. Place container on cookie sheet in center of oven; test with food application before marketing. Covers are designed to fit containers after conventional heating unless stated.

**Packages should not be used in toaster ovens.**

**Microwave Heating:** Loosen cover before heating, cover can be used to prevent splashing. Cover may experience some distortion during microwave heating. Heating times may vary with oven size; test with food application before marketing.



 [www.pactiv.com](http://www.pactiv.com) • 800.476.4300

 **PACTIV**  
Foodservice / Food Packaging

1900 West Field Court / Lake Forest, IL 60045 / 800.476.4300  
2010 Ellesmere Road, Units 6-9 / Scarborough, Ontario M1H 3B1 / Canada / 800.387.3282

03/12 500 Lit# 12-335IH  
© PACTIV LLC 2013