

Precision Handling Gloves

Excellent hand fit and dexterity for incredible comfort and performance


Instructions

1. As shown in the picture, place your right hand on the template with your index finger against Line A and your thumb aligned with the outlined thumb.
2. The measurement on the sizing gauge on Line B is your approximate glove size.

Note:

To ensure a proper fit, print this document 100% to scale (in Print Options, set Page Scaling to "None"). The measurement from left to right between Line A and size 7 (New Sizing) should be 8.5 centimetres.

Alternately, with a ruler, measure the width of your palm in centimetres and gauge sizing as prescribed by the chart.



Flexsor™ 76-400	Black on Grey Nylon / Nitrile	Strong Abrasion Resistance
Flexsor™ 76-600	Black on Black Nylon / Foam Nitrile	Wet and Light Oil Grip
Flexsor™ 78-500	Black on Black Nylon / PU	Strong Breathable Protection
Flexsor™ 78-800	White on White Nylon / PU (Water-based)	Strong Clean Protection